A J COPE & SON LTD

The Oval

London E2 9DU

Telephone: +44 (0) 20 7729 2405 Facsimile: +44 (0) 20 7729 2657

Internet: www.ajcope.co.uk

ELECTRONIC CATALOGUE CUSTOMER'S AMENDMENTS ISSUE 1 — January 2011 Page 1 of 9 pages

	Amendment					
	NEW ITEMS					
	Disposable Cells					
	PMMA. Macro, square, 2-clear sides, 10mm path length. Pack of 100.					
	CA407-25 Macro cells					
	PMMA. Semi-micro, square, 10mm path length. Pack of 100.					
	CA407-30 Semi-micro cells					
========						
	CANCELLATIONS					
	HY605-75 Cancelled, no replacement					
	HY650-20 Cancelled, no replacement HY650-86 Cancelled, no replacement					
	HY654-22 Cancelled, special order only					
	HY654-30 Cancelled, special order only					
	HY654-34 Cancelled, special order only HY654-45 Cancelled, special order only					
	HY654-53 Cancelled, special order only					
	HY654-57 Cancelled, special order only					
	HY654-61 Cancelled, special order only					
	HY654-65 Cancelled, special order only					
========	 					
	NEW ITEMS					
	<u>Identi-tapeTM</u>					
	Generally as LA302 series but supplied in a roll of 55 metres. Supplied in colours as indicated.					
	LA302-12 Blue					
	LA302-17 Green					
	LA302-22 Orange					
	LA302-27 Red LA302-32 White					
	LA302-32 White LA302-37 Yellow					
	ZAZOZ G. TOROW					

ISSUE 1 — January 2011 Page 2 of 9 pages

NEW ITEM

Melting Point Apparatus, Stuart Model SMP20

Based on the MG158-10 but with additional features to improve functionality and ease of use.

- **▲** Maximum temperature 300°C
- **▲** Digital temperature setting and control
- ▲ 4 digit LED display and adjustable resolution 0.1/1°C
- ▲ Pt100 temperature sensor
- ▲ 'Hold' button freezes the display when pressed at viewed melting point
- **▲** Heating rates:
 - 20°C/minute to plateau temperature
 - adjustable ramp rate 1 to 10°C/minute to melt
- ▲ Accepts up to 2 sample tubes
- **▲** Built-in sample illumination
- ▲ Extendable rear feet for optimal viewing angle

Melting Point Apparatus, SMP20

As described. Maximum temperature 300°C. Accuracy ± 1 °C at 20°C, ± 2.5 at 300°C. With Pt100 sensor, digital setting, control adjustable to 0.1/1°C and 4 digit LED readout. Overall 160 x 220 x 170mm W x H x D. Weight 1.8kg. For 230V 50Hz single phase supplies, 75W. Supplied with calibration certificate and 100 melting point tubes, open both ends.

MG165-10 SMP20

NEW ITEM

Microtube plate - Elkay Thermo-Fast

Generally as MW745-series but fully skirted. Supplied in a pack of 50.

MW745-34 Thermo-Fast 0.2ml skirted plates, non-sterile. Pk. 50

ISSUE 1 — January 2011 Page 3 of 9 pages

NEW ITEMS

Disposable Pipette Tips

RefillPro Tip Reload System

Provide a robust, economical solution for tip reloading requirements. Reusable, autoclavable racks manufactured from recycled plastic. Can be fitted with refill "wafers" of 96 non-sterile tips. No special tools or alignment devices are required. A hinged lid protects the tips between uses.

- ▲ Tip capacities: 10µl extended, 200µl, 300µl and 1250µl extended
- ▲ Tips manufactured in 100% virgin polypropylene, certified RNase, Pyrogen and DNase free.
- **▲** Single and multichannel pipettor compatibility
- ▲ Extended pattern tips allow insertion into narrow neck tubes and plates
- ▲ Plastic rack waste reduced by over 60%

Selection chart

Capacity, µl	Colour	For use with
--------------	--------	--------------

1 to 10 (extended) Natural Biohit, Finnpipette, Gilson

P2/P10, Nichiryo, Oxford, Rainin,

Socorex, Volac

1 to 200 Yellow Biohit, Brand, Eppendorf,

Finnpipette, Gilson P200,

Socorex, Volac

1 to 300 (multichannel) Natural Biohit, Brand, Eppendorf,

Finnpipette, Rainin, Socorex, Volac

200 to 1250 (extended) Natural Biohit, Brand, Eppendorf,

Finnpipette, Gilson P1000,

Nichiryo, Oxford, Rainin, Socorex, Volac

RefillPro Tip Reload System

Comprising 10 empty racks (8 - 1250µl tips only) and one refill pack of 40 nested wafers x 96 tips (32 wafers - 1250µl tips only) with capacities as indicated.

PR870-58 1 to 10μl PR870-64 1 to 200μl PR870-67 1 to 300μl PR870-76 200 to 1250μl

RefillPro Refill packs

 40×96 tips (32 $\times 96$ - 1250µl tips) in nested tip wafers with bottom tray and dust cover. Tip capacities as indicated.

PR874-58 1 to 10μl PR874-64 1 to 200μl PR874-67 1 to 300μl PR874-76 200 to 1250μl

RefillPro Racks

Supplied empty, in packs of 20 racks. For tip capacities as indicated.

PR874-90 1 to 10µl, 200µl or 300µl

PR874-95 200 to 1250µl

ISSUE 1 — January 2011 Page 4 of 9 pages

NEW ITEMS

Stainless Steel Barrel Pumps, Burkle

Robust, manual pumps are is suitable for emptying a wide range of liquid containers. All parts in contact with the liquid are electroconductive, stainless steel and suitable for handling flammable liquids. Supplied with removable discharge nozzle. Immersion tube diameter 32mm.

	Submersible length, mm	Total length, mm	Pump volume ml/stroke
PX118-05	360	475	220
PX118-15	570	350	350
PX118-20	910	1030	560

Accessory adaptors, for connections as indicated

PX118-60	Barrel screw joint, PP	
	T-441 / 1 / 11 1 / 11	

R2" internal steel barrel thread

PX118-65 Barrel screw joint, PP

Mauser R2" internal coarse thread

PX118-70 Thead adaptor, PP

2" BSP

PX118-75 PVC barrel plug for 40-70mm

diameter openings

PX120-10 Anti-static set, containing

3 connecting copper cables with clamps in plastic carry case

NEW ITEMS

Otal Foot Pump, Burkle

Polypropylene with PVC stopper. With foot operated squeeze bulb and release button to interrupt the flow. The down tube is extendible and this enables the pump to be used with various sizes of bottle. Liquid is forced into the collecting vessel by squeezing the bulb and the flow can be instantly interrupted by pressing the release button. Excess liquid can be sucked back by pumping and operating the release button. For use as a siphon, additional tubing must be attached to the outlet tube and after pumping the liquid will flow continously. Mounted on a 3-part stopper to fit openings as indicated. Not suitable for pumping highly flammable liquids.

	Flow rate, litres/minute	Stopper size min./max. o.d mm	Outlet diameter, mm
PX127-13	20	30/70	15
PX127-20	26	30/70	18
PX127-23	30	30/70	22

CANCELLATION

QFC8/4S Cancelled, no replacement

ISSUE 1 — January 2011 Page 5 of 9 pages

Page 5 of 9 pages						
	CANCELLA	TION				
	QZ296-94 Cancelled, no replacement					
	NEW ITEMS	S				
		either PTFE or p		or single, one-handed use with thumb operated valve. ampling. Available in 3 sizes and in materials as indicated.		
		Material	Overall length, mm	Capacity, ml		
	SD056-25 SD056-30 SD056-34	PTFE PTFE PTFE	600 1000 2000	150 250 500		
	SD056-40 SD056-45 SD056-50	PP PP PP	600 1000 2000	150 250 500		
	NEW ITEMS	: S				
		l. Crevice-free, w		ror polished surface, preventing materials from being od stuffs and pharmaceutical intermediates.		
		Dia. x scoop length, mm	Capacity approx. ml			
	SH220-10 SH220-20 SH220-25 SH220-35 SH220-50	60 x 120 75 x 140 85 x 155 100 x 180 130 x 220	100 200 250 350 500			
=========	CANCELLATIONS SV340-10 Cancelled, offer SV340-15 SV350-40 Cancelled, offer SV350-30					
=======================================	CANCELLA SV600-15 Ca	TION ncelled, offer SV	======== 600-20			
		, one of the				

ISSUE 1 — January 2011 Page 6 of 9 pages

1 age 0 of 9 pages
NUMER AND
NEW ITEMS
Test Tubes, Elkay
Disposable. Cylindrical with rounded base. Non-sterile. Supplied in packs of 500.
TE730-45 Polystyrene 150 x 16 mm
TE738-45 Polypropylene 150 x 16mm
CANCELLATIONS
TJ875-10 Cancelled, no replacement
TJ875-90 Cancelled, no replacement
TJ875-95 Cancelled, no replacement
TJ877-13 Cancelled, special order only
TJ877-21 Cancelled, special order only
TJ877-25 Cancelled, special order only
TJ877-33 Cancelled, special order only
TJ877-37 Cancelled, special order only
TJ877-41 Cancelled, special order only
TJ877-45 Cancelled, special order only
TJ877-85 Cancelled, no replacement
CANCELLATIONS
WS890-10 Cancelled, offer WS890-12
WS890-15 Cancelled, offer WS890-17
WS890-20 Cancelled, offer WS890-22
WS890-25 Cancelled, offer WS890-27
WS890-30 Cancelled, offer WS890-32
WS890-35 Cancelled, offer WS890-37
WS890-40 Cancelled, offer WS890-42
WS890-45 Cancelled, offer WS890-47
WS890-50 Cancelled, offer WS890-52
WS890-55 Cancelled, offer WS890-57
WS890-60 Cancelled, offer WS890-62
WS890-70 Cancelled, offer WS890-72

ISSUE 1 — January 2011 Page 7 of 9 pages

NEW ITEMS

Single Parameter Meters, Hanna

Dedicated, ion-specific colorimeters offering rapid and accurate determinations in a convenient portable instrument. Ideal for use in water treatment analysis, testing drinking water and quality control.

- **▲** Direct reading LCD
- **▲** Silicon photocell detector
- ▲ LED or tungsten light source with working life as long as the instrument
- **▲** Battery-powered, with automatic shut off after 10 minutes of non-use

Hanna single Parameter Meters

Supplied with two sample cuvettes, 9V PP3 battery giving up to 40 hours operation and instruction manual. Dimensions as indicated. Weight 290g (except WS896-27 which is 420g). Require, but are not supplied with, related accessory reagents.

	Parameter	Range (resolution) mg/l	Filter nm	Overall Price H x W x D mm
WS890-12	Aluminium	0.00 to 1.00 (0.01)	470	180 x 83 x 46
WS890-17	Ammonia	0.00 to 9.99 (0.01)	466	192 x 102 x 67
WS890-22	Bromine	0.00 to 8.00 (0.01)	525	192 x 102 x 67
WS890-27	Free Chlorine	0.00 to 5.00 (0.01)	525	216 x 83 x 65
	Total Chlorine	0.00 to 5.00 (0.01)		
WS890-32	Copper	0.00 to 5.00 (0.01)	555	180 x 83 x 46
WS890-37	Iron	0.00 to 5.00 (0.01)	525	192 x 102 x 67
WS890-42	Nitrate	0.00 to 30.00 (0.1)	525	192 x 102 x 67
WS890-47	Nitrite, low	0.00 to 0.600 (0.01)	525	192 x 102 x 67
WS890-52	Nitrite, high	0.00 to 150.0 (0.1)	585	180 x 83 x 46
WS890-57	Phosphate, low	0.00 to 2.50 (0.01)	610	180 x 83 x 46
WS890-62	Phosphate, high	0.00 to 30.0 (0.1)	470	180 x 83 x 46
WS890-72	Zinc	0.00 to 3.00 (0.01)	585	180 x 83 x 46

T H E E N D

January 2011

CAT. NO.	PRICE £	Per	CODE
CA407-25	8.85	pack	RO
CA407-30	9.30	pack	RO
LA302-12	8.25	roll	FA
LA302-17	8.25	roll	FA
LA302-22	8.25	roll	FA
LA302-27	8.25	roll	FA
LA302-32	8.25	roll	FA
LA302-37	8.25	roll	FA
MG165-10	700.00	each	OS
MW745-34	110.00	pack	FA
PR870-58	35.00	pack	FA
PR870-64	32.00	pack	FA
PR870-67	35.00	pack	FA
PR870-76	102.00	pack	FA
PR874-58	102.00	pack	FA
PR874-64	91.00	pack	FA
PR874-67	96.00	pack	FA
PR874-76	102.00	pack	FA
PR874-90	36.00	pack	FA
PR874-95	45.00	pack	FA
PX118-05	170.00	each	00
PX118-15	170.00	each	00
PX118-20	174.00	each	00
PX118-60	21.00	each	00
PX118-65	23.40	each	00
PX118-70	13.10	each	00
PX118-75	18.90	each	00
PX120-10	41.90	each	00
PX127-13	83.20	each	00
PX127-20	83.40	each	00
PX127-23	86.00	each	00
SD056-25	190.00	each	00
SD056-30	260.00	each	00
SD056-34	370.00	each	00
SD056-40	125.00	each	00
SD056-45	165.00	each	00
SD056-50	257.00	each	00
SH220-10	18.50	each	00
SH220-20	25.90	each	00

Page 9 of 9 Pages

	rage 7 or 7 rages		
SH220-25	28.00	each	00
SH220-35	31.50	each	00
SH220-50	41.70	each	00
TE730-45	43.00	pack	FA
TE738-45	43.00	pack	FA
WS890-12	200.00	each	FB
WS890-17	299.00	each	FB
WS890-22	195.00	each	FB
WS890-27	315.00	each	FB
WS890-32	299.00	each	FB
WS890-37	299.00	each	FB
WS890-42	175.00	each	FB
WS890-47	299.00	each	FB
WS890-52	230.00	each	FB
WS890-57	179.00	each	FB
WS890-62	290.00	each	FB
WS890-72	185.00	each	FB

T H E E N D